




Date Issued: 18.09.09

Supaturf Product Specification Sheet

SupaMarker

Stock code		02045		
What is the machine used for?	A multifunctional aerosol application. The Supamarker can be used in either 2 or 4 wheel set-up.			
Main Features	<ul style="list-style-type: none"> Easily detachable rear wheel assembly Adjustable marking disc with the ability to change line width from 50mm to 75mm Allow the operator to mark out straight over long and short distances Removable front wheel assembly to enable the operator to use the SupaMarker as an effective hand held operator. 			
Recommended for use with		All SupaMark Aerosol Products see stock codes below:		
		Colour	750ml Std	750ml Extra
		White	02521	02519
		Grey	02510	02503
		Yellow	02518	02516
		Red	02515	02514
		D Blue	02507	02506
		Green	02512	02511
		Black	02505	02504
		Orange	02509	02508

Technical Specifications	
Front Axle Assembly	<p>½" galvanised tube front axle with sprung loaded nylon bushes to give 2 position adjustment to the marker discs on the inside of the wheels. Rotating the nylon bushes either end of the axle through 90°, adjustment of the polypropylene marker discs provides the ability to change the line width from 50mm to 75mm.</p> <p>Removal of the 'R' pins either end of the axle allows all the components to be removed to be cleaned or replaced. Axle assembly can be removed from the main handle of the marker by the 'D' clamp thumbscrew to become a hand held applicator.</p>
Wheels	155mm dia tyre width 38mm plain bearing, 12.7mm bore. Black solid rubber tyre, polypropylene centre.
Rear Front Axle Assembly	Rear axle frame and supports can be assembled and removed by two hand wheels on the main handle of the marker. When the rear axle assembly is detached it becomes ideal for circles and designs.

Supaturf South Africa – Main dealer/Head Office/KwaZulu-Natal:

231 Lothian Road, Durban North, 4051, South Africa

Email: info@supaturf.co.za ,Tel: 0315632513, Fax: 0315635251, Cell: 0836532513

SOUTH AFRICA



Date Issued: 18.09.09

Frame	Manufactured from 19.1mm 1.6 gauge round lacquered triple zinc coated galvanised tube.
Aerosol Holder	<p>Manufactured from galvanised steel plate to hold a 400ml or a 750ml aerosol can.</p> <p>Aerosol holder is adjustable via a hand wheel to position the can in the correct position. Lowest position for 50mm line width and moved up to its highest position for a 75mm line. So as to give the wider spray pattern when further away from the marker discs.</p> <p>Hinged sprung actuator lever depresses the aerosol can nozzle by operating the hand trigger. Aerosol can lock positioned on the main handle tube by a push lock and pole clamp thumbscrew. Aerosol cannot be activated by pushing down whilst positioned in the holder.</p>
Hand-Grip	3 position handgrip for steadying the applicator whilst marking. Can be positioned for left or right-handed people or in an upright position.
Weight & Dimensions	
Mode One Weight Complete	5.4kg
Mode Two Rear Wheels Removed	2.9kg
Mode Three Front Wheels Removed	1.5kg
Boxed Weight	7.0kg
Boxed Dimensions	Length 1105mm, height 560mm, width 285mm

Contact us at: www.supaturf.co.za

**Supaturf South Africa – Main dealer/Head Office/KwaZulu-Natal:
231 Lothian Road, Durban North, 4051, South Africa
Email: info@supaturf.co.za ,Tel: 0315632513, Fax: 0315635251, Cell: 0836532513**